SRE-2010E/SRE-2010E0S ELITE STRAIGHT OUTDOOR STAIRLIFT TECHNICAL APPLICATION DRAWING

TECHNICAL DATA/SPECIFICATION

MODEL: SRE-2010E, SRE-2010EOS OUTDOOR ELITE STRAIGHT RAIL STAIRLIFT

RATED LOAD: 400 LBS, ONE PASSENGER

POWER SOURCE: 24 VOLT DC COMPRISED OF (2) 7 AMP/HR

12 VOLT SEALED BATTERIES

110 VOLT AC 1.5 AMP, 24 VOLT DC 2 AMP CONTINUOUS MONITORING CHARGER.

DRIVE: 24 VOLT DC DIRECT DRIVE GEAR-MOTOR, 2 POLE RATED .68 HP, 58:1 RIGHT ANGLE SELF LOCKING GEARBOX, 41.5 RPM NO LOAD RPM OUTPUT SPEED.

SUSPENSION: RACK & PINION - INTEGRATED 8DP GEAR RACK ON RAIL WITH A SPUR GEAR ON THE OUTPUT SHAFT OF THE GEAR BOX.

BRAKING: DYNAMIC MOTOR BRAKING THROUGH THE MOTOR CONTROLLER, SELF LOCKING WORM GEAR, AND

ELECTRO-MECHANICAL MOTOR BRAKE.
CONTROLS: CONTINUOUS PRESSURE ARMREST SWITCH LOCATED
ON THE ARM REST AND WALL MOUNTED CALL/SEND

CONTROLS LOCATED AT BOTH THE TOP AND BOTTOM LANDINGS.

ANGLES: (SRE-2010E) 0 TO 45 DEGREES (CUSTOM TO 50 DEGREES) (SRE-2010EOS) 30 TO 45 DEGREES (CUSTOM TO 50 DEGREES)

RIGHT OR LEFT HAND ORIENTATIONS

FINAL LIMIT SWITCH STANDARD KEYED CALL/SEND CONTROLS STANDARD

KEYED CALL/3END CONTROLS STANDARD KEYED CONTROL ON CHAIR STANDARD OPTIONS:


1) XL SEAT

2) PACKAGE WITH OVERSPEED SAFETY BRAKE (SRE-2010EOS)

3) SEAT WITH ATTACHED CANOPY**

NOT AVAILABLE WITH XL SEAT OPTION


SIDE VIEWS




ILS-00799

SHEET 1 OF 2

REV. 2 (7530)(09/22/22)(BHM)





©Bruno Independent Living Aids, Inc.

NOTES:

1. ALL SEATS ADJUST UP 3" IN 1" INCREMENTS.
2. STANDARD FOOTREST ADJUSTMENTS UP 1 1/4" IN 5/8" INCREMENTS.


SRE-2010E/SRE-2010E0S ELITE STRAIGHT OUTDOOR STAIRLIFT TECHNICAL APPLICATION DRAWING


VIEWS REFLECT STANDARD COVER WITH SRE-2010EOS CARRIAGE.

UP POSITION

15 3/8" FOLDED

POSITION





ILS-00799 SHEET 2 OF 2 REV. 2 (7530)(09/22/22)(BHM)

BRUNO ©Bruno Independent Living Aids, Inc.